

ANTISTATICO

ANTISTATIC LIQUID



FEATURES AND USE

ANTISTATICO sprayed on gauze fitted on dust mop or fitted on Lamiwell or sprayed directly on dust mop replacement make easy the sweeping and dusting floors.

Spray ANTISTATICO on a cloth to wipe dust from furniture.

ANTISTATICO contains aliphatic solvents and substances that retain dust.

ANTISTATICO contains an emulsion to make easy dust detachment during washing.



METHOD OF USE:

Spray ANTISTATICO in uniform way on the dry gauze, previously folded up on dust mop or Lamiwell. Remove the dust from the surfaces always keeping it in the front of dust mop or cloth.

DILUTION :

AS IS

PACK SIZE:

Bottle 750ml – 12pcs/carton

TECHNICAL DATA:

Physical state : Liquid

Colour: Light blue

Odour: Floral note

pH as is 7,5 +/-0,5

S.W. 1,000 Kg/Lt.

COMPOSITION :

See point N° 2 of safety data sheet. Ingredient conforming to: CE Reg. 648/2004

CAUTIONS: